



More information on the website  
radwag.com/en/info,w1,LRF

# C315.4P.600/1500.C Pallet Scale



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

Plus/Minus Control

Percent Weighing

Totalizing

Parts counting

Internal battery

Peak hold

Newton unit measurement

GLP Procedures

Animal weighing

ALIBI Memory

## Datasheet

Metrological parameters	
Maximum capacity [Max]	600/1500 kg
Minimum load	4 kg
Readability [d]	200/500 g
Verification unit [e]	200/500 g
Tare range	-1500 kg
OIML Class	III

Physical parameters	
Display	LCD (backlit)
Weighing pan dimensions	840×1200 mm
Device dimensions	1322×840×85 mm
Packaging dimensions	1400×900×430 mm
Scale mass with indicator	43 kg
Cable length	3 m
Construction	
Protection class	IP 65 construction, IP 67 cell, IP 43 indicator
Communication interface	
Communication interface	RS232
Optional interfaces	RS232
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz and battery
Power consumption max.	5 W
Operation time on batteries	max 8h
Environmental conditions	
Operating temperature	-10 ÷ +40 °C
Relative humidity	10% ÷ 85% RH no condensation



Extra payment for verification



## Accessories

Power Adapters  
 RS 232 cables (scale - printer)  
 Stands, wall mounting kits and mounting brackets  
 Cigarette lighter receptacle power supply cables  
 Displays  
 Displays  
 RS 232, RS 485 cables


RS 232 – Ethernet Converter  
 AP2-1 Current Loop Unit  
 RS 232, RS 485 cables  
 RS 232 – USB Converter  
 RS 232 cables (scale - printer)  
 RS 232 – RS 485 Converter  
 Receipt Printer

## Software

- RAD Key [WX-010-0005]
- R-Lab [WX-010-0080]

- R-Panel [WX-010-0187]
- Scale Editor 2.1 [WX-010-0173]

## Device dimensions



Transport of the pallet scale using casters and handles.