



CY10.15.C3.K.M3 Multifunctional Scale


WP-125-0037

More information on the website
radwag.com/us/info,w1,M4C



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



IR sensors



Animal weighing



Statistical Quality Control



Wi-Fi

Datasheet

Maximum capacity [Max]	15 kg
Minimum load	10 g
Readability [d]	5 g
Verification unit [e]	5 g
Tare range	-15 kg
Max readability for non-verified scale	0,5 g
Stabilization time	3 s
Adjustment	external

OIML Class	III
Physical parameters	
Leveling system	manual
Display	10" graphic colour touchscreen
Cable length	2,5 m
Weighing pan dimensions	500×700 mm
Packaging dimensions	850×800×270 mm
Net weight	22,7 kg
Gross weight	26,5 kg
Construction	
Protection class	IP 65 construction, IP 43 terminal
Housing	steel + ABS
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,6A max; 10–19W*
Operating temperature	
Operating temperature	-10 – +40 °C
Storage temperature	
Storage temperature	-25 – +70 °C
Multiple range	
Multiple range	YES
Features of use	
Max number of platforms	max.2

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



Accessories (Additional Fee)

MediaBox

Mild steel powder coated weighing platforms

RFID Tags

Power Adapters

Additional Weighing platforms Module

Mild steel powder coated weighing platforms

Additional modules

Platforms in plastic casing

Protective cover for balances

Barcode scanners

Label Printers

RS 232, RS 485 cables

Stands, wall mounting kits and mounting brackets

Fingerprint Reader

RS 232 – USB Converter

Receipt Printer

Software (Additional Fee)

• E2R Weighing [WX-010-0099]

• RAD Key [WX-010-0005]

• RADWAG Remote Desktop [WX-010-0107]

• E2R Weighing Records [WX-010-0038]

• Label Editor R02 [WX-010-0094]

• Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions

