



More information on the website  
[radwag.com/us/info,w1,MC5](http://radwag.com/us/info,w1,MC5)

# H315.15/30.HR3.K Waterproof Scale With Stainless Steel Load Cell



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit measurement



Animal weighing

## Datasheet

|                            |               |
|----------------------------|---------------|
| Maximum capacity [Max]     | 15 / 30 kg    |
| Minimum load               | 100 g         |
| Readability [d]            | 5 / 10 g      |
| Verification unit [e]      | 5 g           |
| Tare range                 | -30 kg        |
| OIML Class                 | III           |
| <b>Physical parameters</b> |               |
| Display                    | LCD (backlit) |
| Cable length               | 2,5 m         |

| Physical parameters         |   |
|-----------------------------|---|
| Weighing pan dimensions     | 410×410 mm  |
| Packaging dimensions        | 510×510×270 mm  |
| Net weight                  | 15,5 kg   |
| Gross weight                | 17,3 kg   |
| Construction                |   |
| Protection class            | IP 68 construction, IP 68 cell, IP 68 (1h max)/69 terminal      |
| Construction                | Stainless steel AISI316   |
| Communication interface     |   |
| Communication interface     | RS232, USB  |
| Optional interfaces         | RS232 or RS485 or 4IN/4OUT or Ethernet or analog output 4-20 mA |
| Power supply                |   |
| Power supply                | 100 – 240 V AC 50/60 Hz   |
| Optional power supply       | internal rechargeable battery                                   |
| Operation time on batteries | max 7h  |
| Operating temperature       |   |
| Operating temperature       | -10 – +40 °C  |
| Storage temperature         |   |
| Storage temperature         | -25 – +70 °C  |
| Relative humidity           |   |
| Relative humidity           | 10% – 85% RH no condensation                                    |



Extra payment for verification



## Accessories

RS 232 cables (scale - printer)

Antivibration tables

Displays

RS 232 cables (scale - Ethernet)

RS 232, RS 485 cables

RS 232 – Ethernet Converter

USB adapter

Receipt Printer

USB cable (scale - printer)

Stands, wall mounting kits and mounting brackets

RS 232 – USB Converter

Roller table

RS 232, RS 485 cables

## Software

• RAD Key [WX-010-0005]

• Scale Editor - EWAG 2.1 [WX-010-0173]

• R Panel [WX-010-0187]

## Device dimensions



|                |           | A1  | A2  | B       | C1  | C2  | D    | E    | L    |
|----------------|-----------|-----|-----|---------|-----|-----|------|------|------|
| H315...HR2.M   | 250 x 300 | 246 | 306 | 104 ± 3 | 208 | 268 | ~525 | ~483 |      |
| H315...HR2.K   | 250 x 300 | 246 | 306 | 104 ± 3 | 208 | 268 | -    | -    | 1,5m |
| H315...HR3.M   | 410 x 410 | 410 | 410 | 98 ± 2  | 370 | 370 | ~525 | ~587 |      |
| H315...HR3.K   | 410 x 410 | 410 | 410 | 98 ± 2  | 370 | 370 | -    | -    | 2,5m |
| H315...HR4.M   | 500 x 500 | 497 | 497 | 155 ± 5 | 400 | 400 | ~767 | ~650 |      |
| H315...HR4.K   | 500 x 500 | 497 | 497 | 155 ± 5 | 400 | 400 | -    | -    | 2,5m |
| H315...HR3/5.M | 400 x 600 | 597 | 397 | 155 ± 5 | 500 | 300 | ~767 | ~550 |      |
| H315...HR3/5.K | 400 x 600 | 597 | 397 | 155 ± 5 | 500 | 300 | -    | -    | 2,5m |
| H315...HR5.M   | 600 x 600 | 597 | 597 | 155 ± 5 | 500 | 500 | ~767 | ~750 |      |
| H315...HR5.K   | 600 x 600 | 597 | 597 | 155 ± 5 | 500 | 500 | -    | -    | 2,5m |