



More information on the website  
[radwag.com/de/info,w1,MR6](https://radwag.com/de/info,w1,MR6)

# DWM HPE Dynamische Etikettenwaage



The drawings, photos and graphics used are for illustrative purposes only.

## Technische Daten

Messtechnische Parameter	
Wägebereich [Max]	3000 - 7500 g
Zifferschritt [d]	1 - 5 g
OIML-Klasse	XIII (1), Y (a)
Physikalische Parameter	
Display	12" grafisch farbiger Touchscreen
Labelling throughput	60 St./min
Print resolution	300/600 dpi
Print speed	max 300 mm/s
Print width	106/162,6 mm
Label width	114/174 mm
Roller external diameter	305 mm
Print method	Thermisch / Thermotransfer
Kommunikationsschnittstellen	
Schnittstellen	Ethernet, USB, RS232, I / O

## Konstruktion

Konstruktion

pulverbeschichteter Stahl / Edelstahl

Wägesystem

elektromagnetischer Modul



## Zubehör

Thermische Drucker