



More information on the website  
[radwag.com/en/info,w1,MR6](http://radwag.com/en/info,w1,MR6)

# DWM HPE Labelling Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	3000 - 7500 g
Readability [d]	1 - 5 g
OIML Class	XIII (1), Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Labelling throughput	60 pcs/min
Print resolution	300/600 dpi
Print speed	max 300 mm/s
Print width	106/162.6 mm
Label width	114/174 mm
Roller external diameter	305 mm
Print method	thermal / thermal transfer
Communication interface	
Communication interface	Ethernet, USB, RS232, I / O

## Construction

Construction

mild steel / Stainless steel

Weighing module

electromagnetic weighing module



## Accessories

Receipt Printer