



More information on the website  
[radwag.com/it/info,w1,MR6](http://radwag.com/it/info,w1,MR6)

# Bilancia di etichettatura dinamica DWM HPE

WK-105-004\_



The drawings, photos and graphics used are for illustrative purposes only.

## Specifiche

### Parametri metrologici

Portata massima [Max]	3000 – 7500 g
Divisione [d]	1 – 5 g
Classe OIML	XIII (1), Y (a)

### Parametri fisici

Display	12" graphic colour touchscreen
Labelling throughput	60 pcs/min
Print resolution	300/600 dpi
Print speed	max 300 mm/s
Print width	106 / 162,6 mm
Label width	114 / 174 mm
Roller external diameter	305 mm
Print method	thermal / thermal transfer

### Interfaccia di comunicazione

Interfaccia	Ethernet, USB, RS232, I / O
-------------	-----------------------------

## Costruzione

Costruzione	mild steel / Stainless steel
Modulo di pesata	electromagnetic weighing module

## Components and software

Sistema operativo	Microsoft Windows 11 IoT
-------------------	--------------------------



## Accessori (Additional Fee)

Stampanti di ricevuta