



More information on the website  
[radwag.com/it/info,w1,MR6](http://radwag.com/it/info,w1,MR6)

# DWM HPE Labelling Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

## Specifiche

Parametri metrologici	
Portata massima [Max]	3000 – 7500 g
Divisione [d]	1 – 5 g
Classe OIML	XIII (1), Y (a)
Parametri fisici	
Display	12" graphic colour touchscreen
Labelling throughput	60 pcs/min
Print resolution	300/600 dpi
Print speed	max 300 mm/s
Print width	106 / 162,6 mm
Label width	114 / 174 mm
Roller external diameter	305 mm
Print method	thermal / thermal transfer
Interfaccia di comunicazione	
Interfaccia	Ethernet, USB, RS232, I / O

## Costruzione

Costruzione

mild steel / Stainless steel

Modulo di pesata

electromagnetic weighing module



## Accessori

Stampanti di ricevuta