



More information on the website
radwag.com/us/info,w1,MR6

DWM HPE Labelling Checkweigher

WK-105-0000



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| | |
|----------------------------|--------------------------------|
| Maximum capacity [Max] | 3000 – 7500 g |
| Readability [d] | 1 – 5 g |
| OIML Class | XIII (1), Y (a) |
| Physical parameters | |
| Display | 12" graphic colour touchscreen |
| Labelling throughput | 60 pcs/min |
| Print resolution | 300/600 dpi |
| Print speed | max 300 mm/s |
| Print width | 106 / 162,6 mm |
| Label width | 114 / 174 mm |
| Roller external diameter | 305 mm |
| Print method | thermal / thermal transfer |
| Communication interface | Ethernet, USB, RS232, I / O |

Construction

Construction

mild steel / Stainless steel

Weighing module

electromagnetic weighing module



Accessories (Additional Fee)

Receipt Printer