



More information on the website
radwag.com/us/info,w1,MR6

DWM HPE Labelling Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Maximum capacity [Max]	3000 - 7500 g
Readability [d]	1 - 5 g
OIML Class	XIII (1), Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Labelling throughput	60 pcs/min
Print resolution	300/600 dpi
Print speed	max 300 mm/s
Print width	106/162,6 mm
Label width	114/174 mm
Roller external diameter	305 mm
Print method	thermal / thermal transfer
Communication interface	Ethernet, USB, RS232, I / O

Construction

Construction

mild steel / Stainless steel

Weighing module

electromagnetic weighing module



Accessories

Receipt Printer