



More information on the website
radwag.com/en/info,w1,MVB

C315.4P.3000.C Pallet Scale



The drawings, photos and graphics used are for illustrative purposes only.

Functions

 Plus/Minus Control

 Percent Weighing

 Totalizing

 Parts counting

 Internal battery

 Peak hold

 Newton unit measurement

 GLP Procedures

 Animal weighing

 ALIBI Memory

Datasheet

| Metrological parameters | |
|--|----------|
| Maximum capacity [Max] | 3000 kg |
| Minimum load | 20 kg |
| Readability [d] | 1000 g |
| Tare range | -3000 kg |
| Max readability for non-verified scale | 1000 g |
| OIML Class | III |

| Physical parameters | |
|-----------------------------|---|
| Display | LCD (backlit) |
| Weighing pan dimensions | 840×1200 mm |
| Device dimensions | 1322×840×85 mm |
| Packaging dimensions | 1400×900×430 mm |
| Scale mass with indicator | 43 kg |
| Cable length | 3 m |
| Construction | |
| Protection class | IP 65 construction, IP 67 cell, IP 43 indicator |
| Communication interface | |
| Communication interface | RS232 |
| Optional interfaces | RS232 |
| Electrical parameters | |
| Power supply | 100 – 240 V AC 50/60 Hz and battery |
| Power consumption max. | 5 W |
| Operation time on batteries | max 8h |
| Environmental conditions | |
| Operating temperature | -10 ÷ +40 °C |
| Relative humidity | 10% ÷ 85% RH no condensation |



Extra payment for verification



Accessories

Power Adapters
 RS 232 cables (scale - printer)
 Stands, wall mounting kits and mounting brackets
 Cigarette lighter receptacle power supply cables
 Displays
 Displays
 RS 232, RS 485 cables

RS 232 – Ethernet Converter
 AP2-1 Current Loop Unit
 RS 232, RS 485 cables
 RS 232 – USB Converter
 RS 232 cables (scale - printer)
 RS 232 – RS 485 Converter
 Receipt Printer

Software

- RAD Key [WX-010-0005]
- R-Lab [WX-010-0080]

- R-Panel [WX-010-0187]
- Scale Editor 2.1 [WX-010-0173]

Device dimensions



Transport of the pallet scale using casters and handles.