



# Multi-Track DWM H2 Checkweigher

WK-105-00\_

More information on the website  
[radwag.com/en/info,w1,MWB](http://radwag.com/en/info,w1,MWB)



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	1500 – 7500 g
Minimum load	4 – 20 g
Readability [d]	0.2 – 1 g
Verification unit [e]	0.2 – 1 g
Tare range	-1500 – -7500 g
Max readability for non-verified scale	0.2 – 1 g
Expanded reading unit	0.01 – 0.5 g
OIML Class	XIII (1), Y (a)
Construction	
Protection class	IP 55, IP 65
Keypad	touch screen
Construction	mild steel / Stainless steel
Communication interface	
Communication interface	Ethernet, USB, RS232, I / O, Modbus, ProfiNet (option), ProfiBus (option)

### Electrical parameters

Power supply 100 – 240 V AC 50/60 Hz

### Environmental conditions

Operating temperature +5 – +40 °C

### Features of use

Conveyor velocity 1.6 m/s



## Accessories (Additional Fee)

RS 232 cables (scale - ZEBRA printer)  
RS 232, RS 485 cables  
Tunnel Detectors  
Keypad, external switches

USB adapter  
Receipt Printer  
USB cable (scale - printer)

## Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]