



More information on the website  
[radwag.com/us/info,w1,MWB](http://radwag.com/us/info,w1,MWB)

# Multi-Track DWM H2 Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Maximum capacity [Max]	1500 – 7500 g
Minimum load	4 – 20 g
Readability [d]	0,2 – 1 g
Verification unit [e]	0,2 – 1 g
Tare range	-1500 – -7500 g
Max readability for non-verified scale	0,2 – 1 g
Expanded reading unit	0,01 – 0,5 g
OIML Class	XIII (1), Y (a)
<b>Construction</b>	
Protection class	IP 55, IP 65
Keypad	touch screen
Construction	mild steel / Stainless steel
Communication interface	Ethernet, USB, RS232, I / O, Modbus, ProfiNet (option), ProfiBus (option)

Power supply	100 – 240 V AC 50/60 Hz
Operating temperature	+5 – +40 °C
<b>Features of use</b>	
Conveyor velocity	1,6 m/s



## Accessories

RS 232 cables (scale - ZEBRA printer)  
 RS 232, RS 485 cables  
 Tunnel detectors  
 Keypad, external switches

USB adapter  
 Receipt Printer  
 USB cable (scale - printer)

## Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]