



More information on the website
radwag.com/us/info,w1,N0Y

XA 21/52.5Y.M Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

| | |
|------------------------|---------|
| Maximum capacity [Max] | 21/52 g |
| Minimum load | 0,1 mg |
| Readability [d] | 1/5 µg |

| | |
|-------------------------------------|--|
| Verification unit [e] | 1 mg |
| Tare range | -52 g |
| Standard repeatability [5% Max] | 1,5 µg |
| Standard repeatability [Max] | 6 µg |
| Standard minimum weight (USP) | 3 mg |
| Standard minimum weight (U=1%, k=2) | 0,3 mg |
| Permissible repeatability [5% Max] | 2,4 µg |
| Permissible repeatability [Max] | 8 µg |
| Linearity | ±20 µg |
| Eccentric load deviation | 20 µg |
| Sensitivity time drift | 1×10 ⁻⁶ /Year×Rt |
| Stabilization time | ~3,5 s |
| Adjustment | internal (automatic) |
| OIML Class | I |
| Physical parameters | |
| Leveling system | półautomatyczny - LevelSENSING |
| Display | 10" graphic colour touchscreen |
| Weighing chamber doors | manual |
| Delivery components | Microbalance, weighing pan, weighing pan shield, bottom cover, power supply, brush, fabric dust cover. |
| Weighing chamber dimensions | 168×160×228 mm |
| Weighing pan dimensions | ø30 mm |
| Packaging dimensions | 750×492×595 mm |
| Net weight | 9,8 kg |
| Gross weight | 14,3 kg |
| Construction | |
| Protection class | IP 43 |
| Communication interface | 2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot |
| Power supply | Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max* |
| Operating temperature | +10 – +40 °C |
| Operating temperature change rate | ±0,3°C/1h (±1°C/8h) |
| Relative humidity | 40% – 80% |
| Relative humidity change rate | ±1%/h (±4%/8h) |

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
RFID Tags
Antivibration tables
Power Adapters
RS 232, RS 485 cables
Additional modules
Anti-Draft Chamber for Microbalances
Professional Weighing Tables
Protective cover for balances
Barcode scanners
Automatic feeders
MICRO-KIT - Set of Holders for Microscale Glassware

Label Printers
THBR 2.0 System - Ambient Conditions Monitoring
RS 232, RS 485 cables
Protective cover for balances
Adapters for pipettes calibration
Anti-Draft Chamber for XA 4Y and XA 5Y Balances
Weighing dishes
Antistatic ionizer
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter
Under-pan weighing

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions

