



More information on the website  
[radwag.com/us/info,w1,N1T](http://radwag.com/us/info,w1,N1T)

# CY10.60/150.C2.K.M3 Multifunctional Scale



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



IR sensors



Animal weighing



Statistical Quality Control



Wi-Fi

## Datasheet

|                        |             |
|------------------------|-------------|
| Maximum capacity [Max] | 60 / 150 kg |
| Minimum load           | 400 g       |
| Readability [d]        | 20 / 50 g   |
| Verification unit [e]  | 20 g        |
| Tare range             | -150 kg     |
| Stabilization time     | 2 s         |
| Adjustment             | external    |
| OIML Class             | III         |

| Physical parameters     |  |
|-------------------------|--|
| Leveling system         | manual   |
| Display                 | 10" graphic colour touchscreen   |
| Cable length            | 2,5 m  |
| Weighing pan dimensions | 400×500 mm   |
| Packaging dimensions    | 720×620×210 mm   |
| Net weight              | 12,1 kg  |
| Gross weight            | 14,1 kg  |
| Construction            |  |
| Protection class        | IP 43  |
| Housing                 | steel + ABS  |
| Communication interface | 2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot   |
| Power supply            | Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A<br>Balance: 12 – 15V DC 1,6A max; 10–19W* |
| Operating temperature   | -10 – +40 °C   |
| Storage temperature     | -25 – +70 °C   |
| Multiple range          | YES  |
| Features of use         |  |
| Max number of platforms | max.2  |

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



## Accessories

### MediaBox

Mild steel powder coated weighing platforms  
RFID Tags  
Power Adapters  
Additional Weighing platforms Module  
Mild steel powder coated weighing platforms  
Additional modules  
Platforms in plastic casing

### Protective cover for balances

Barcode scanners  
Label Printers  
RS 232, RS 485 cables  
Stands, wall mounting kits and mounting brackets  
Fingerprint Reader  
RS 232 – USB Converter  
Receipt Printer

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

## Device dimensions

