



More information on the website  
[radwag.com/us/info,w1,N00](http://radwag.com/us/info,w1,N00)

# C32.6.D2 Multifunctional Scale



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Labelling



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Newton unit measurement



Statistics



IR sensors



Under-pan weighing



GLP Procedures



Replaceable unit



ALIBI Memory

## Datasheet

|  |       |
|--|-------|
| Maximum capacity [Max]                 | 6 kg  |
| Minimum load                           | 40 g  |
| Readability [d]                        | 2 g   |
| Tare range                             | -6 kg |
| Max readability for non-verified scale | 0,2 g |
| OIML Class                             | III   |

| Physical parameters         |  |
|-----------------------------|--|
| Display                     | 5" graphic colour  |
| Weighing pan dimensions     | 195×195 mm   |
| Packaging dimensions        | 530×310×150 mm   |
| Net weight                  | 3,4 kg   |
| Gross weight                | 4,5 kg   |
| Cable length                | 1 m  |
| Construction                |  |
| Protection class            | IP 43  |
| Housing                     | ABS plastic  |
| Weighing pan material       | Stainless steel AISI304  |
| Communication interface     | 2×RS232, USB-A, USB-B, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi |
| Power supply                | 100 – 240 V AC 50/60 Hz  |
| Power consumption max.      | 10 W   |
| Optional power supply       | internal rechargeable battery                                  |
| Operation time on batteries | operation time up to 5 h                                       |
| Operating temperature       | -10 ÷ +40 °C   |

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



## Accessories

Displays  
 Power Adapters  
 RS 232 cables (scale - printer)  
 Cigarette lighter receptacle power supply cables  
 Barcode scanners  
 RS 232, RS 485 cables  
 Label Printers  
 Displays

Displays  
 Keypad, external switches  
 Stands, wall mounting kits and mounting brackets  
 Additional modules  
 Receipt Printer  
 RS 232, RS 485 cables  
 RS 232 cables (scale - printer)

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- Alibi Reader PC Software [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

## Device dimensions



C32.D2



C32.F1.R



C32.F1.M



C32.F1.K