



More information on the website
radwag.com/en/info,w1,NXL

H315.4N.1500.H2.LD Stainless Steel Ramp Scale



The drawings, photos and graphics used are for illustrative purposes only.

Functions

 Plus/Minus Control

 Percent Weighing

 Totalizing

 Parts counting

 Internal battery

 Peak hold

 Newton unit measurement

 Animal weighing

Datasheet

Metrological parameters

| | |
|--|----------|
| Maximum capacity [Max] | 1500 kg |
| Minimum load | 10 kg |
| Readability [d] | 500 g |
| Tare range | -1500 kg |
| Max readability for non-verified scale | 100 g |
| OIML Class | III |

Physical parameters

| | |
|-------------------------|---------------|
| Display | LCD (backlit) |
| Weighing pan dimensions | 1100×1200 mm |

| Physical parameters | |
|-----------------------------|---|
| Packaging dimensions | 1640×1590×580 mm |
| Net weight | 200 kg |
| Gross weight | 330 kg |
| Cable length | 3 m |
| Construction | |
| Protection class | IP 68 construction, IP 68 (1h max)/69 indicator |
| Communication interface | |
| Communication interface | RS232, USB |
| Optional interfaces | RS232 or RS485 or 4IN/4OUT or Ethernet or analog output 4-20 mA |
| Electrical parameters | |
| Power supply | 100 – 240 V AC 50/60 Hz |
| Optional power supply | internal rechargeable battery |
| Operation time on batteries | max 7h |
| Environmental conditions | |
| Operating temperature | -10 ÷ +40 °C |
| Relative humidity | 10% ÷ 85% RH no condensation |



Extra payment for verification



Accessories

RS 232 cables (scale - printer)
 Displays
 RS 232 cables (scale - Ethernet)
 RS 232, RS 485 cables
 RS 232 – Ethernet Converter
 USB adapter

Receipt Printer
 USB cable (scale - printer)
 Stands, wall mounting kits and mounting brackets
 RS 232 – USB Converter
 RS 232, RS 485 cables

Software

- RAD Key [WX-010-0005]
- R-Lab [WX-010-0080]

- R-Panel [WX-010-0187]
- Scale Editor 2.1 [WX-010-0173]

Device dimensions



| | A [mm] | B [mm] | C [mm] | D [mm] |
|--------------------|--------|--------|--------|--------|
| H315.4N.150.H1.LD | 840 | 860 | 45 | 426 |
| H315.4N.300.H1.LD | 840 | 860 | 45 | 426 |
| H315.4N.600.H1.LD | 840 | 860 | 45 | 426 |
| H315.4N.150.H2.LD | 1100 | 1200 | 45 | 426 |
| H315.4N.300.H2.LD | 1100 | 1200 | 45 | 426 |
| H315.4N.600.H2.LD | 1100 | 1200 | 45 | 426 |
| H315.4N.300.H3.LD | 1200 | 1500 | 45 | 426 |
| H315.4N.600.H3.LD | 1200 | 1500 | 45 | 426 |
| H315.4N.1500.H2.LD | 1100 | 1200 | 52 | 476 |
| H315.4N.1500.H3.LD | 1200 | 1500 | 52 | 476 |
| H315.4N.300.H4.LD | 1500 | 1500 | 52 | 476 |
| H315.4N.600.H4.LD | 1500 | 1500 | 52 | 476 |
| H315.4N.1500.H4.LD | 1500 | 1500 | 52 | 476 |