



More information on the website  
[radwag.com/en/info,w1,00D](http://radwag.com/en/info,w1,00D)

# XA 520.5Y Analytical Balance



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  Under-pan weighing
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

## Datasheet

### Metrological parameters

Maximum capacity [Max]	520 g
Minimum load	-

<b>Metrological parameters</b>	
Readability [d]	0.1 mg
Verification unit [e]	-
Tare range	-520 g
Standard repeatability [5% Max]	0.07 mg
Standard repeatability [Max]	0.18 mg
Standard minimum weight (USP)	140 mg
Standard minimum weight (U=1%, k=2)	14 mg
Permissible repeatability [5% Max]	0.12 mg
Permissible repeatability [Max]	0.25 mg
Linearity	±0.5 mg
Eccentric load deviation	0.4 mg
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times R_t$
Stabilization time	1.3 s
Adjustment	internal (automatic)
OIML Class	-
<b>Physical parameters</b>	
Leveling system	półautomatyczny - LevelSENSING
Display	10" graphic colour touchscreen
Weighing chamber doors	manual
Delivery components	Analytical Balance, weighing pan, weighing pan shield, bottom cover, brush, fabric dust cover, power supply.
Weighing chamber dimensions	168×160×228 mm
Weighing pan dimensions	ø100 mm
Packaging dimensions	750×492×595 mm
Net weight	9.8 kg
Gross weight	14.3 kg
<b>Construction</b>	
Protection class	IP 43
<b>Communication interface</b>	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
<b>Electrical parameters</b>	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.6A max*
<b>Environmental conditions</b>	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0.3°C/1h (±1°C/8h)
Relative humidity	20% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

\* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories

MediaBox  
RFID Tags  
Antivibration Tables  
Power Adapters  
RS 232, RS 485 cables  
Holders for laboratory flasks  
Density determination KIT  
Additional modules  
Holders for test tubes and filters  
Professional Weighing Tables  
Protective cover for balances  
Barcode scanners  
Automatic feeders

Label Printers  
THBR 2.0 System - Ambient Conditions Monitoring  
RS 232, RS 485 cables  
Protective cover for balances  
Under-pan weighing  
Anti-Draft Chamber for XA 4Y and XA 5Y Balances  
Weighing dishes  
Antistatic ionizer  
Receipt Printer  
Fingerprint Reader  
RS 232 – USB Converter  
Under-pan weighing

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

## Device dimensions

