



More information on the website
radwag.com/en/info,w1,0EE

DWM Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	750 ÷ 7500 g
Minimum load	2 ÷ 20 g
Readability [d]	0.1 ÷ 1 g
Verification unit [e]	0.1 ÷ 1 g
Tare range	-750 ÷ -7500 g
Max readability for non-verified scale	0.1 ÷ 1 g
Expanded reading unit	0.05 ÷ 0.5 g
OIML Class	XIII (1), Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Construction	
Protection class	IP 55, IP 65
Keypad	touch screen
Construction	mild steel / Stainless steel

Communication interface	
Communication interface	Ethernet, USB, RS232, I / O
Environmental conditions	
Operating temperature	+5 ÷ +40 °C
Features of use	
Conveyor velocity	1.6 m/s



Accessories

RS 232 cables (scale - ZEBRA printer)
 Tunnel Detectors
 RS 232, RS 485 cables
 Keypad, external switches

USB adapter
 Receipt Printer
 USB cable (scale - printer)

Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]