



More information on the website
radwag.com/en/info,w1,0EO

MW-01-2 Mass Converter



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
OIML Class	III
Maximum quantity of verification units	10000 e
Minimum volatge per verification unit	0.5 μ V
Minimum load cell impedance	80 Ω
Maximum load cell impedance	1200 Ω
Load cell excitation voltage	5V DC
Maximum increase of signal	19.5 mV
Connection of load cells	4 or 6 wires + shield
Construction	
Protection class	IP 66
Housing	aluminum
Communication interface	
Communication interface	RS232

Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Environmental conditions	
Operating temperature	-10 ÷ +40 °C
Physical parameters	
Packaging dimensions	300×250×130 mm
Net weight	1 kg
Gross weight	1.4 kg
Multiple range	YES
Features of use	
Max number of platforms	1

Compatible with


RS 232 – USB Converter

Displays

Software

- RAD Key [WX-010-0005]
- R-Lab [WX-010-0080]
- MW Manager [WX-010-0113]
- RADWAG Development Studio [WX-010-0104]

Device dimensions



MW-01

