



# MA 110.5Y.WH Moisture Analyzer

WL-304-0036

More information on the website  
[radwag.com/us/info,w1,OEP](http://radwag.com/us/info,w1,OEP)



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Statistics
-  IR sensors
-  GLP Procedures
-  Replaceable unit
-  Statistical Quality Control
-  ALIBI Memory
-  Drying modes
-  Samples drying
-  Moisture content analysis
-  Dry mass determination
-  Wi-Fi

## Datasheet

Maximum capacity [Max]	110 g
Readability [d]	1 mg
Tare range	-110 g
Adjustment	external
Maximum sample weight	110 g
Heating module	halogen
Moisture content repeatability	±0,05 % (sample ~ 2 g), ±0,01 % (sample ~ 10 g)
Moisture content readability	0,001 %

Drying temperature range	Max 250 °C
<b>Physical parameters</b>	
Leveling system	semi-automatic – LevelSENSING
Display	10" graphic colour touchscreen
Weighing chamber	automatic
Delivery components	Moisture Analyzer, disposable pan x 10, cross-shaped holder, drying pan handle, weighing pan shield, fabric dust cover, power cord
Maximum sample height	20 mm
Weighing pan dimensions	ø90, h= 8 mm
Packaging dimensions	540x610x470 mm
Net weight	5,3 kg
Gross weight	6,8 kg
<b>Construction</b>	
Protection class	IP 43
<b>Features of use</b>	
Display mode	%D, %M, %R, g
Drying method	4 drying profiles (standard, fast, step, mild)
Finish mode	4 modes (automatic, manual, time-defined, user-defined)
Additional functions	sample traceability
<b>Communication interface</b>	
Communication interface	2xUSB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
<b>Power supply</b>	
Power supply	100 – 120 V AC 50/60 Hz or 200-240 V AC 50/60 Hz
Power consumption	6 W
Heating module power	450 W
<b>Operating temperature</b>	
Operating temperature	+10 – +40 °C
<b>Mass indication control</b>	
Mass indication control	External mass standard 50 g, 100 g, 200 g, depending on the type of moisture analyzer (additional equipment)
<b>Drying temperature control</b>	
Drying temperature control	One- or two-point, depending on the drying profile (additional equipment: GT105k-12/Z Control Thermometer)
<b>Moisture content indication control</b>	
Moisture content indication control	Certified MV Test Set (additional equipment)
<b>Drying temperature adjustment</b>	
Drying temperature adjustment	Three-point adjustment at defined temperatures, programmable values (additional equipment: GT105k-12/Z Control Thermometer)

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories (Additional Fee)

Antivibration tables  
 Moisture analyzer accessories  
 Additional modules  
 Barcode scanners  
 Receipt Printer

Fingerprint Reader  
 RS 232, RS 485 cables  
 RS 232 cables (scale - printer)  
 RS 232 – RS 485 Converter

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

## Device dimensions

