



More information on the website
radwag.com/en/info,w1,OKX

High Resolution Platforms PL.32.HRP.EX.H



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| Metrological parameters | |
|-------------------------|----------------------|
| Maximum capacity [Max] | 32 kg |
| Minimum load | 5 g |
| Preload range | 4 kg |
| Readability [d] | 0.1 g |
| Tare range | -32 kg |
| Repeatability | 0.1 g |
| Linearity | ±0.3 g |
| Stabilization time | 2 s |
| Adjustment | internal (automatic) |
| Physical parameters | |
| Cable length | 10 m |
| Weighing pan dimensions | 360×280 mm |
| Device dimensions | 360×313×170 mm |
| Packaging dimensions | 560×473×370 mm |
| Net weight | 18.7 kg |

| Construction | |
|--------------------------|--|
| Protection class | IP 66 / 67 |
| Construction | Stainless steel AISI304 |
| Weighing pan material | Stainless steel AISI304 |
| ATEX Certification | II 3G Ex ic IIC T4 Gc II 3D Ex ic IIIC T60°C Dc |
| IECEX Certification | Ex ic IIC T4 Gc Ex ic IIIC T60°C Dc |
| Communication interface | |
| Communication interface | RS485 |
| Electrical parameters | |
| Power supply | 100 – 240 V AC 50/60 Hz |
| Environmental conditions | |
| Operating temperature | +10 – +40 °C |
| Relative humidity | 15% – 80% |



Accessories

PUE HX5.EX Weighing Terminal
Antivibration Tables

Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX
Weighing Terminal
Receipt Printer

Software

- MWMH Manager [WX-010-0103]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]

Device dimensions



PL.16 - 32.HRP.H



PL.62-2000.HRP.H

| Scale type | A1 | A2 | H |
|-----------------------|------|------|-------|
| PL.(16-32).HRP.H | 360 | 280 | 180±5 |
| PL.(62-150).HRP.H | 500 | 400 | 180±5 |
| PL.150.2.HRP.H | 500 | 500 | 180±5 |
| PL.(150.1-300).HRP.H | 800 | 600 | 180±5 |
| PL.(300.1-1100).HRP.H | 1000 | 800 | 180±5 |
| PL.(2000).HRP.H | 1250 | 1000 | 180±5 |

Dimensions in mm