



More information on the website
radwag.com/en/info,w1,OPA

C32.3.D2 Multifunctional Scale



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Labelling



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Newton unit measurement



Statistics



IR sensors



Under-pan weighing



GLP Procedures



Replaceable unit



ALIBI Memory

Datasheet

Metrological parameters

Maximum capacity [Max]	3 kg
Minimum load	20 g
Readability [d]	1 g
Tare range	-3 kg
Max readability for non-verified scale	0,1 g
OIML Class	III

Physical parameters	
Display	5" graphic colour
Protection class	IP 43
Weighing pan dimensions	195×195 mm
Packaging dimensions	500×310×150 mm
Net weight	3,4 kg
Gross weight	4,3 kg
Communication interface	
Communication interface	2×RS232, USB-A, USB-B, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Power consumption max.	10 W
Optional power supply	internal rechargeable battery
Operation time on batteries	operation time up to 5 h
Environmental conditions	
Operating temperature	-10 ÷ +40 °C
Construction	
Housing	ABS plastic
Weighing pan material	stainless steel AISI304

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

Displays
 RS 232 cables (scale - printer)
 Cigarette lighter receptacle power supply cables
 Barcode scanners
 RS 232, RS 485 cables

Label Printers
 Keypad, external switches
 Stands, wall mounting kits and mounting brackets
 Receipt Printer

Software

RAD-KEY
 Label Editor R02
 RADWAG Development Studio
 R.Barcode

LabVIEW Driver
 R-LAB
 E2R System

Device dimensions



C32.D2



C32.F1.R



C32.F1.M



C32.F1.K