



# MPS.T.6000.R1 Weighing Module

WX-016-0350

More information on the website  
[radwag.com/us/info,w1,P7R](http://radwag.com/us/info,w1,P7R)



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Maximum capacity [Max]	6000 g
Readability [d]	0,1 g
Repeatability	0,15 g
Warm-up time after connection to power	1 h
Stabilization time	3 s
Adjustment	external
Maximum preload	600 g
<b>Construction</b>	
Protection class	IP 43
Housing	aluminum
Weighing pan material	Stainless steel
Communication interface	RS232, max 115,2 kbps, Radwag ASCII protokół
Power supply	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Moduł: 12V DC

Operating temperature	+10 – +40 °C
Relative humidity	40% – 80%
<b>Physical parameters</b>	
Weighing pan dimensions	ø65
Device dimensions	220x70x75 mm
Net weight	0,9 kg



## Accessories (Additional Fee)

RS 232, RS 485 cables

## Software (Additional Fee)

• R Panel [WX-010-0187]

## Device dimensions

