



More information on the website
radwag.com/en/info,w1,PDD

VLINE80L-2W Receipt Printer



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Paper width	80 mm
Outer diameter of paper/roll length	83 mm / 80 mm
Print speed	max 250 mm/s
Communication interface	
Communication interface	USB, Wi-Fi
Electrical parameters	
Power supply	100 – 240V AC 50/60 Hz / 24 V DC 2.5 A
Environmental conditions	
Operating temperature	0 ÷ +40 °C
Relative humidity	10% ÷ 90% RH
Physical parameters	
Device dimensions	147×147×195 mm
Net weight	1.8 kg

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

Compatible with

H315 HR Waterproof Platform Scale
MA X7.IC.A Moisture Analyzer
MAS1 Modules
WPY Multifunctional Scale
Microbalance for Pipette Calibration MYA 5Y.P
C32 Multifunctional Scale
MA 5Y Moisture Analyzer
C315 Platform scale
Microbalance for Filters MYA 5Y.F
TMX H Stainless steel Multifunctional Scale
WLY Scales for PGC
MA X2.IC.A Moisture Analyzer
AS X7 Analytical Balance
PS X2 Precision Balance
AS X2 PLUS Analytical Balance
TMX Multifunctional Scale
C315.D Baby Scale
WLC Precision Balance
PS R2 Precision Balance
C315.4P2 Beam Scales
WLC X2 Precision Balance
H315 4H Stainless Steel Platform Scale
H315 4P2.H Stainless steel Beam Scales
WLC X7 Precision Balance
PS X2 Balances for PGC
DWT/RC/HYF Checkweighers
H315 H Waterproof Platform Scale
MA X2.A Moisture Analyzer
HY10 Multifunctional Scale
RS 232 cables (scale - printer)
HY10 H Stainless Steel Multifunctional Scale
H315.4 H/Z Stainless Steel Platform Scale, pit version
H315 4N.H Stainless Steel Ramp Scale
C315.4 Platform Scale
C32.PM Precision Balance
MA X7.A Moisture Analyzer
C315.O Personal Scale
H315 4N.H.LD Stainless Steel Ramp Scale
PS X7 Precision Balance
WPY Scales for PGC

C315.4P pallet scales
WAY 5Y.KO Manual Mass Comparator
MA 5Y.IC Moisture Analyzer
MA R Moisture Analyzer
AS 5Y Analytical Balance
PUE 7.1.HRP High Resolution Scale
PS R2.H Precision Balance
HY10.H Scales for PGC
WTC Precision Balance
Dust-Free Cabinets for Printers
H315 4C Platform Scale
C315.OW Personal Scale
XA 5Y.F Analytical Balance for Filters
WLY Precision Balance
H315 2K Overhead Track Scales
APP 5Y.KO Manual Mass Comparator
H315 4P.H Stainless Steel Pallet Scales
WLC C/2 Precision Balance
H315 4I.S Livestock Scales
PS R1 Precision Balance
MA X2.A Moisture Analyzers
5Y.PM.KB Manual Mass Comparator
USB cable (scale - printer)
AS R2 PLUS Analytical Balance
PUE 7.1 Weighing Terminal
PUE 5 Weighing Terminal
PS 5Y Precision Balance
PMV 5Y Moisture Analyzer
XA 5Y.KO Manual Mass Comparator
H315 4I.H Stainless Steel Livestock Scales
PUE C315 Weighing Terminal
UYA 5Y.KO Manual Mass Comparator
AS R1 PLUS Analytical Balances
C315.4B Bed Scale
PUE H315 Weighing Terminal
DWM Checkweighers
C315.K Chair Scale
Roller Scales
H315 Stainless Steel Overhead Track Scales
C315.8B Ramps Bed Scale