



More information on the website
radwag.com/us/info,w1,PES

PUE H315 Weighing Terminal



The drawings, photos and graphics used are for illustrative purposes only.

Functions

 Plus/Minus Control

 Percent Weighing

 Totalizing

 Parts counting

 Internal battery

 Peak hold

 Newton unit measurement

 GLP Procedures

 Animal weighing

 ALIBI Memory

Datasheet

OIML Class	III
Maximum quantity of divisions from converter	838 860 ×10
Maximum quantity of verification units	6000 e
Minimum volatge per verification unit	0,4 μV
Maximum voltage per verification unit	3,25 μV
Minimum load cell impedance	50 Ω
Maximum load cell impedance	1200 Ω
Load cell excitation voltage	5V DC

Maximum increase of signal	39 mV
Connection of load cells	4 or 6 wires + shield
Physical parameters	
Display	LCD (backlit)
Device dimensions	208×145×80 mm
Packaging dimensions	300×250×130 mm
Net weight	1,9 kg
Gross weight	2,2 kg
Construction	
Protection class	IP 66 / IP 67 / IP 69
Keypad	microswitch
Housing	Stainless steel
Communication interface	
Communication interface	RS232, USB
Optional interfaces	RS232 or RS485 or 4IN/4OUT or Ethernet or analog output 4-20 mA
Power supply	
Power supply	100 – 240 V AC 50/60 Hz
Optional power supply	internal rechargeable battery
Operation time on batteries	max 7h
Operating conditions	
Operating temperature	-10 ÷ +40 °C
Storage temperature	-10 ÷ +50 °C
Relative humidity	10% ÷ 80% RH no condensation
Number of buttons	5
Multiple range	1 or 2 ranges
Additional LCD display	WD-4/1 (option)



Compatible with

Waterproof stainless steel platforms
Mild steel powder coated weighing platforms
RS 232 cables (scale - printer)
RS 232, RS 485 cables
Mild steel powder coated weighing platforms
Displays
RS 232 cables (scale - Ethernet)
USB adapter

Receipt Printer
Additional modules
USB cable (scale - printer)
Stands, wall mounting kits and mounting brackets
RS 232 – USB Converter
RS 232, RS 485 cables
RS 232 – RS 485 Converter

Software

- RAD Key [WX-010-0005]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- R Panel [WX-010-0187]
- RADWAG Development Studio [WX-010-0104]

Device dimensions

