



More information on the website  
[radwag.com/en/info,w1,PT7](http://radwag.com/en/info,w1,PT7)

# AVK 1000.5Y.CP Automatic Constant Pressure Mass Comparator



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
E1 Calibration Range	100 g ÷ 1 kg
E2 Calibration Range	100 g ÷ 1 kg
F1 Calibration Range	100 g ÷ 1 kg
F2 Calibration Range	100 g ÷ 1 kg
Maximum capacity [Max]	1002 g
Readability [d]	0.1 µg
Standard repeatability [5% Max]	0.7 µg
Standard repeatability [Max]	1 µg
Permissible repeatability	1.5 µg
Electric compensation range	-1 g ÷ +2 g
Stabilization time	60 s
Adjustment	external
Physical parameters	
Display	10" graphic colour touchscreen
Magazine positions	6

Physical parameters	
Weighing pan dimensions	ø100 mm
Vacuum chamber dimensions	965×745×1150 mm
Pressure range	constant
Object diameters	cylindrical ø (22-95)×110; spherical ø (40-100) mm
Weighing device dimensions	965×745×1700 mm
Controlling device dimensions	249×170×72 mm
Net weight (without table)	250 kg
Net weight (with table)	650 kg
Supplementary weights external	500 g, 800 g, 900 g
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Environmental conditions	
Operating temperature	+15 ÷ +30 °C
Operating temperature change rate	±0.1°C/12h
Relative humidity	45% ÷ 60%

Repeatability in a vacuum under model ambient conditions for 6 ABBA cycles

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories

RFID Tags  
 Additional modules  
 Protective cover for balances  
 Barcode scanners  
 RS 232, RS 485 cables

THBR 2.0 System - Ambient Conditions Monitoring  
 Receipt Printer  
 Fingerprint Reader  
 RS 232, RS 485 cables  
 RS 232 cables (scale - printer)

## Software

• RMCS Lite [WX-010-0164]

• RMCS System Network Management of Calibration Process [WX-010-0048]

## Device dimensions

