



More information on the website
radwag.com/en/info,w1,QOS

PLC/60/C2 Platform



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	60 kg
Readability [d]	20 g
Construction	
Protection class	IP 65
Construction	mild steel St3S
Weighing pan material	Stainless steel AISI304
Physical parameters	
Weighing pan dimensions	400×500 mm
Packaging dimensions	720×620×210 mm




Accessories



PUE CY10 Weighing Terminal
 CY10 Multifunctional Scale
 PUE 5 Weighing Terminal
 CY10 Precision Balance
 PUE C32 Weighing Terminal

PUE 7.1 Weighing Terminal
 PUE HX7 Weighing Terminal
 PUE C315 Weighing Terminal
 PUE HY10 Weighing Terminal
 PUE H315 Weighing Terminal

Device dimensions



PL/D2



PLC/F1



PLC/C2
PLC/C3



PL/H
PL/HR

Platform type	A1	A2	H
PL/D2	238	216	82±3
PLC/F1	300	300	70±3
PLC/C2	402	502	103±3
PLC/C3	701	501	130±5
PL/H1 / PL/HR1	150	200	85±3
PL/H2 / PL/HR2	250	300	103±3
PL/H3 / PL/HR/3	410	410	98±3
PL/H3/5 / PL/HR/3/5	400	600	155±3
PL/H4 / PL/HR/4	500	500	155±3
PL/H5 / PL/HR/5	600	600	155±3
PL/H6	800	800	135±3

dimensions in mm