



More information on the website
radwag.com/us/info,w1,QTM

C32.120.PM Precision Balance



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Labelling



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Newton unit measurement



Statistics



IR sensors



GLP Procedures



Animal weighing



Density determination



Replaceable unit



ALIBI Memory

Datasheet

Maximum capacity [Max]	120 kg
Minimum load	-
Preload range	12 kg
Readability [d]	0,2 g
Tare range	-120 kg
Minimum weight (USP)	164 g

Minimum weight (U=1%,k=2)	16,4 g
Repeatability (Max)	0,2 g
Repeatability (5% Max)	0,082 g
Linearity	±0,6 g
Stabilization time	1 s
Adjustment	internal (automatic)
Physical parameters	
Leveling system	manual
Display	5" graphic colour
Weighing pan dimensions	400×500 mm
Packaging dimensions	710×610×240 mm
Net weight	22 kg
Gross weight	24,5 kg
Construction	
Protection class	IP 43
Communication interface	2×RS232, USB-A, USB-B, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi
Power supply	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Balance: 10 – 12V DC 1A max
Operating temperature	+10 ÷ +40 °C

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

Displays
 Antivibration tables
 Power Adapters
 RS 232 cables (scale - printer)
 Cigarette lighter receptacle power supply cables
 Professional Weighing Tables
 Barcode scanners

RS 232, RS 485 cables
 Displays
 Displays
 Stands, wall mounting kits and mounting brackets
 Additional modules
 Receipt Printer
 RS 232, RS 485 cables

Software

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- E2R Weighing Records [WX-010-0038]
- Alibi Reader PC Software [WX-010-0114]

Device dimensions

