



More information on the website
radwag.com/en/info,w1,QXZ

CY10.15.F1.K.M3 Multifunctional Scale



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



IR sensors



Animal weighing



Statistical Quality Control



Wi-Fi

Datasheet

Metrological parameters	
Maximum capacity [Max]	15 kg
Minimum load	100 g
Readability [d]	5 g
Verification unit [e]	5 g
Tare range	-15 kg
Max readability for non-verified scale	0.5 g
Stabilization time	2 s

Metrological parameters	
Adjustment	external
OIML Class	III
Physical parameters	
Leveling system	manual
Display	10" graphic colour touchscreen
Weighing pan dimensions	300×300 mm
Packaging dimensions	500×390×410 mm
Net weight	6.3 kg
Gross weight	7.1 kg
Cable length	1 m
Multiple range	YES
Construction	
Protection class	IP 43
Housing	steel + ABS
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	12÷15V DC
Power consumption	1A
Environmental conditions	
Operating temperature	-10 ÷ +40 °C
Storage temperature	-25 ÷ +70 °C
Features of use	
Max number of platforms	max.2

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
Mild steel powder coated weighing platforms
RFID Tags
Power Adapters
Additional Weighing platforms Module
Mild steel powder coated weighing platforms
Additional modules
Platforms in plastic casing

Protective cover for balances
Barcode scanners
Label Printers
RS 232, RS 485 cables
Stands, wall mounting kits and mounting brackets
Fingerprint Reader
RS 232 – USB Converter
Receipt Printer

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]

Device dimensions

