



C315.4P2.2000.C1 Beam Scale

WP-240-0002


More information on the website
radwag.com/en/info,w1,R26




The drawings, photos and graphics used are for illustrative purposes only.


Functions


 Plus/Minus Control


 Percent Weighing

 Totalizing


 Parts counting


 Internal battery

 Peak hold

 Newton unit measurement

 GLP Procedures

 Animal weighing

 ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	2000 kg
Minimum load	20 kg
Readability [d]	1000 g
Tare range	-2000 kg
OIML Class	III
Physical parameters	
Display	LCD (backlit)

Physical parameters	
Cable length	3 m + 5 m
Weighing pan dimensions	2 pcs 2 m
Device dimensions	2000×120×105 mm
Scale mass with indicator	53 kg
Construction	
Protection class	IP 65 construction, IP 67 cell, IP 43 terminal
Communication interface	
Communication interface	RS232
Optional interfaces	RS232
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz and battery
Power consumption max.	5 W
Operation time on batteries	max 8h
Environmental conditions	
Operating temperature	-10 – +40 °C
Relative humidity	10% – 85% RH no condensation



Additional fee for verification



Accessories (Additional Fee)

Power Adapters

RS 232 cables (scale - printer)

Stands, wall mounting kits and mounting brackets

Cigarette lighter receptacle power supply cables

Displays

Displays

RS 232 – Ethernet Converter

AP2-1 Current Loop Unit

RS 232, RS 485 cables

RS 232 – USB Converter

RS 232 cables (scale - printer)

RS 232 – RS 485 Converter

Receipt Printer

Software (Additional Fee)

• RAD Key [WX-010-0005]

• R-Lab [WX-010-0080]

• R-Panel [WX-010-0187]

• Scale Editor 2.1 [WX-010-0173]

Device dimensions



Scale type	A	B	H	D
WPT/4P2 600C	120	1200	85	1100
WPT/4P2 1500C	120	1200	85	1100
WPT/4P2 3000C	120	1200	85	1100
WPT/4P2 2000C1	120	2000	105	1900
WPT/4P2 2000C2	120	2500	105	2400
WPT/4P2 4000C1	120	2000	155	1880
WPT/4P2 4000C2	120	2500	155	2380
WPT/4P2 6000C1	120	2000	155	1880
WPT/4P2 6000C2	120	2500	155	2380

dimensions in mm



Scale type	A	B	H	D
C315.4P2 600.C	120	1200	85	1100
C315.4P2 1500.C	120	1200	85	1100
C315.4P2 3000.C	120	1200	85	1100
C315.4P2 2000.C1	120	2000	105	1900
C315.4P2 4000.C1	120	2500	105	2400
C315.4P2 6000.C1	120	2000	155	1880
C315.4P2 2000.C2	120	2500	155	2380
C315.4P2 4000.C2	120	2000	155	1880
C315.4P2 6000.C2	120	2500	155	2380

dimensions in mm