



More information on the website
radwag.com/en/info,w1,RBW

DWM Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	7500 g
Readability [d]	0.1 g
Tare range	-7500 g
OIML Class	XIII (1), Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Construction	
Protection class	IP 55, IP 65
Keypad	touch screen
Construction	mild steel / Stainless steel
Communication interface	
Communication interface	Ethernet, USB, RS232, I / O

Environmental conditions

Operating temperature +5 ÷ +40 °C

Features of use

Capacity max 500 pcs/min



Accessories

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Label Printers

Tunnel Detectors

USB adapter

Receipt Printer

USB cable (scale - printer)