



More information on the website
radwag.com/en/info,w1,RHG

MYA 21.4Y Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Autotest



Dosing



Percent Weighing



Parts counting



Formulation



Newton unit
measurement



Statistics



Checkweighing



IR sensors



GLP Procedures



Animal weighing



Pipettes Calibration



Air density correction



Differential weighing



Ambient conditions
monitoring



Replaceable unit



Statistical Quality Control



Wi-Fi

Datasheet

Metrological parameters

Maximum capacity [Max]	21 g
Minimum load	100 µg
Readability [d]	1 µg
Verification unit [e]	1 mg

Metrological parameters	
Tare range	-21 g
Standard repeatability [5% Max]	1 µg
Standard repeatability [Max]	3 µg
Standard minimum weight (USP)	2 mg
Standard minimum weight (U=1%, k=2)	0.2 mg
Permissible repeatability [5% Max]	1.6 µg
Permissible repeatability [Max]	4 µg
Linearity	±7 µg
Eccentric load deviation	7 µg
Sensitivity offset	$4 \times 10^{-6} \times R_t$
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times R_t$
Stabilization time	max 10 s
Adjustment	internal (automatic)
OIML Class	I
Sensitivity temperature drift	$1 \times 10^{-6} / ^\circ\text{C} \times R_t$
Physical parameters	
Leveling system	semi-automatic - LevelSENSING
Display	5.7" resistive colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, terminal, weighing pan, weighing pan shield, glass lid, power supply, pincette, brush, fabric dust cover.
Weighing chamber dimensions	ø90×90 mm
Weighing pan dimensions	ø26 mm
Packaging dimensions	750×492×595 mm
Net weight	9.1 kg
Gross weight	16.6 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×RS232, 2×USB-A, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.1A max
Environmental conditions	
Operating temperature	+10 ÷ +40 °C
Operating temperature change rate	±0.3°C/1h (±1°C/8h)
Relative humidity	40% ÷ 80%
Relative humidity change rate	±1%/h (±4%/8h)

Repeatability is expressed as a standard deviation from 10 weighing cycles.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

Accessories

Automatic Variable-Volume Pipettes
RS 232, RS 485 cables
Workstation for Pipettes Calibration
Label Printers
Chamber for filter weighing

Antivibration Tables
RS 232, RS 485 cables
RS 232 – USB Converter
Professional Weighing Tables

Software

- RAD Key [WX-010-0005]
- R-Lab [WX-010-0080]

- R-Pipettes [WX-010-0026]
- RADWAG Development Studio [WX-010-0104]

Device dimensions

