




More information on the website
radwag.com/ja/info,w1,S4J

AS 120.5Y

WL-104-0528



The drawings, photos and graphics used are for illustrative purposes only.



Autotest



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



Newton unit measurement



Statistics



Checkweighing



IR sensors



Under-pan weighing



GLP Procedures



Animal weighing



Pipettes Calibration



Air density correction



Density determination



Differential weighing



Ambient conditions monitoring



Statistical Quality Control



Packaged Goods Control



ALIBI Memory



Wi-Fi

[Max]

120 g

1 mg

Ważności	
Ważność [d]	0,01 mg
Ważność [e]	1 mg
Ważność	-120 g
Ważność [5% Max]	0,01 mg
Ważność [Max]	0,025 mg
Ważność (USP)	20 mg
Ważność (U=1%, k=2)	2 mg
Ważność [5% Max]	0,02 mg
Ważność [Max]	0,04 mg
Ważność	±0,07 mg
Ważność	2 s
Ważność	Ważności (Ważności)
OIML	I
Ważności	
Ważności	- LevelSENSING
Ważności	10" Ważności + Ważności Ważności
Ważności	7WażnościWażności
Ważności	, , , , , , , ,
Ważności	190×190×227 mm
Ważności	ø90 Ważności + ø85 Ważności mm
Ważności	600×400×550 mm
Ważności	7,14 kg
Ważności	10,5 kg
Ważności	
Ważności	IP 43
Ważności	
Ważności	7
Ważności	
Ważności	Ważności
Ważności	
Ważności	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Ważności	
Ważności	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A : 12 – 15V DC 1,6A max; 10–19W*
Ważności	
Ważności	+10 – +40 °C
Ważności - Ważności Ważności	THBR 2.0 System, THBR BOX, THB P, THB W, THB S
Ważności	40% – 80%

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



ⓧⓧⓧⓧⓧ (Additional Fee)

ⓧⓧⓧ
 ⓧⓧⓧⓧⓧⓧⓧⓧⓧ
 ⓧⓧⓧⓧⓧ
 RS 232ⓧRS 485 ⓧⓧⓧ
 ⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧ
 ⓧⓧⓧⓧⓧⓧⓧ
 ⓧⓧⓧⓧⓧ
 ⓧⓧⓧⓧⓧ
 ⓧⓧⓧⓧⓧ
 USB cable (ⓧⓧⓧ - ⓧⓧⓧⓧ)
 ⓧⓧⓧⓧⓧⓧⓧⓧ
 ⓧⓧⓧⓧⓧⓧ
 ⓧⓧⓧⓧⓧⓧ

ⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧ
 ⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧ
 THBR 2.0 ⓧⓧⓧ - ⓧⓧⓧ - ⓧⓧⓧⓧⓧⓧ
 ⓧⓧⓧ
 ⓧⓧⓧⓧⓧⓧⓧⓧⓧⓧ
 ⓧⓧⓧⓧⓧⓧ
 ⓧⓧⓧⓧⓧ
 RS 232ⓧRS 485 ⓧⓧⓧ
 ⓧⓧⓧⓧⓧⓧ
 RS 232 ⓧⓧⓧ (ⓧⓧⓧ - ⓧⓧⓧⓧ)
 RS 232 - RS 485 ⓧⓧⓧⓧ

ⓧⓧⓧⓧⓧ (Additional Fee)

- [WX-010-0099]
- [WX-010-0005]
- [WX-010-0107]
- [WX-010-0173]

- [WX-010-0038]
- [WX-010-0094]
- [WX-010-0080]
- [WX-010-0104]

ⓧⓧⓧⓧⓧⓧⓧ

