



More information on the website  
[radwag.com/en/info,w1,S9H](http://radwag.com/en/info,w1,S9H)

# DWT/RC SY Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

<b>Metrological parameters</b>	
Maximum capacity [Max]	10 – 600 kg
Minimum load	0.1 – 4 kg
Readability [d]	5 – 200 g
Tare range	-10 – -600 kg
<b>Physical parameters</b>	
Display	5.7" resistive colour touchscreen
<b>Construction</b>	
Protection class	IP 55
<b>Communication interface</b>	
Communication interface	RS232, RS485
<b>Environmental conditions</b>	
Operating temperature	-10 – +40 °C

## Features of use

Capacity	max 50 pcs/min
Conveyor velocity	0.1 – 0.5 m/s
Speed	0.1 – 0.5 m/s



## Accessories

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Keypad, external switches

Receipt Printer

USB cable (scale - printer)

## Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]