



# C315.4P2.600.C Beam Scale

WP-240-0007

More information on the website  
[radwag.com/en/info,w1,SKA](http://radwag.com/en/info,w1,SKA)



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

 Plus/Minus Control

 Percent Weighing

 Totalizing

 Parts counting

 Internal battery

 Peak hold

 Newton unit measurement

 GLP Procedures

 Animal weighing

 ALIBI Memory

## Datasheet

Metrological parameters	
Maximum capacity [Max]	600 kg
Minimum load	4 kg
Readability [d]	200 g
Tare range	-600 kg
Max readability for non-verified scale	200 g
OIML Class	III

Physical parameters	
Display	LCD (backlit)
Cable length	3 m + 5 m
Weighing pan dimensions	2 pcs 1.2 m
Device dimensions	1200×120×85 mm
Scale mass with indicator	37 kg
Construction	
Protection class	IP 67 construction, IP 43 terminal
Communication interface	
Communication interface	RS232
Optional interfaces	RS232
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz and battery
Power consumption max.	5 W
Operation time on batteries	max 8h
Environmental conditions	
Operating temperature	-10 – +40 °C
Relative humidity	10% – 85% RH no condensation



Additional fee for verification



## Accessories (Additional Fee)

Power Adapters

RS 232 cables (scale - printer)

Stands, wall mounting kits and mounting brackets

Cigarette lighter receptacle power supply cables

Displays

Displays

RS 232 – Ethernet Converter

AP2-1 Current Loop Unit

RS 232, RS 485 cables

RS 232 – USB Converter

RS 232 cables (scale - printer)

RS 232 – RS 485 Converter

Receipt Printer

## Software (Additional Fee)

• RAD Key [WX-010-0005]

• R-Lab [WX-010-0080]

• R-Panel [WX-010-0187]

• Scale Editor 2.1 [WX-010-0173]

## Device dimensions



Scale type	A	B	H	D
WPT/4P2 600C	120	1200	85	1100
WPT/4P2 1500C	120	1200	85	1100
WPT/4P2 3000C	120	1200	85	1100
WPT/4P2 2000C1	120	2000	105	1900
WPT/4P2 2000C2	120	2500	105	2400
WPT/4P2 4000C1	120	2000	155	1880
WPT/4P2 4000C2	120	2500	155	2380
WPT/4P2 6000C1	120	2000	155	1880
WPT/4P2 6000C2	120	2500	155	2380

dimensions in mm



Scale type	A	B	H	D
C315.4P2 600.C	120	1200	85	1100
C315.4P2 1500.C	120	1200	85	1100
C315.4P2 3000.C	120	1200	85	1100
C315.4P2 2000.C1	120	2000	105	1900
C315.4P2 4000.C1	120	2500	105	2400
C315.4P2 6000.C1	120	2000	155	1880
C315.4P2 2000.C2	120	2500	155	2380
C315.4P2 4000.C2	120	2000	155	1880
C315.4P2 6000.C2	120	2500	155	2380

dimensions in mm