



More information on the website
radwag.com/en/info,w1,SSP

XA 6.5Y.M.A.S Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Automatic sliding door
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Metrological parameters

| | |
|------------------------|--------|
| Maximum capacity [Max] | 6.1 g |
| Minimum load | 0.1 mg |

| Metrological parameters | |
|-------------------------------------|--|
| Readability [d] | 1 µg |
| Verification unit [e] | 1 mg |
| Tare range | -6.1 g |
| Standard repeatability [5% Max] | 1.3 µg |
| Standard repeatability [Max] | 3.5 µg |
| Standard minimum weight (USP) | 2.6 mg |
| Standard minimum weight (U=1%, k=2) | 0.26 mg |
| Permissible repeatability [5% Max] | 2 µg |
| Permissible repeatability [Max] | 5 µg |
| Linearity | ±9 µg |
| Eccentric load deviation | 7 µg |
| Sensitivity time drift | 1×10 ⁻⁶ /Year×Rt |
| Stabilization time | ~3.5 s |
| Adjustment | internal (automatic) |
| OIML Class | I |
| Physical parameters | |
| Leveling system | automatyczny - Reflex Level System |
| Display | 10" graphic colour touchscreen |
| Weighing chamber doors | automatic |
| Weighing chamber dimensions | 199×170×217 mm |
| Weighing pan dimensions | ø30 mm + 2× intended for stents |
| Packaging dimensions | 750×492×595 mm |
| Net weight | 14.5 kg |
| Gross weight | 22.5 kg |
| Construction | |
| Protection class | IP 43 |
| Electrical parameters | |
| Power supply | Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.4A max* |
| Environmental conditions | |
| Operating temperature | +10 – +40 °C |
| Operating temperature change rate | ±0.3°C/1h (±1°C/8h) |
| Relative humidity | 40% – 80% |
| Relative humidity change rate | ±1%/h (±4%/8h) |

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
RFID Tags
Antivibration Tables
Power Adapters
Protective cover for balances
Additional modules
Anti-Draft Chamber for Microbalances
Professional Weighing Tables
Protective cover for balances
Barcode scanners

RS 232, RS 485 cables
Label Printers
THBR 2.0 System - Ambient Conditions Monitoring
RS 232, RS 485 cables
Anti-Draft Chamber for XA 4Y and XA 5Y Balances
Antistatic ionizer
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter
Under-pan weighing

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]