

























More information on the website
radwag.com/us/info,w1,SSP

XA 6.5Y.M.A.S Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Automatic sliding door
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Maximum capacity [Max]	6,1 g
Minimum load	0,1 mg
Readability [d]	1 µg

Verification unit [e]	1 mg
Tare range	-6,1 g
Standard repeatability [5% Max]	1,3 µg
Standard repeatability [Max]	3,5 µg
Standard minimum weight (USP)	2,6 mg
Standard minimum weight (U=1%, k=2)	0,26 mg
Permissible repeatability [5% Max]	2 µg
Permissible repeatability [Max]	5 µg
Linearity	±9 µg
Eccentric load deviation	7 µg
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times R_t$
Stabilization time	~3,5 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatyczny - Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Weighing chamber dimensions	199×170×217 mm
Weighing pan dimensions	ø30 mm + 2× intended for stents
Packaging dimensions	750×492×595 mm
Net weight	14,5 kg
Gross weight	22,5 kg
Construction	
Protection class	IP 43
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max*
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3°C/1h (±1°C/8h)
Relative humidity	40% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
RFID Tags
Antivibration tables
Power Adapters

RS 232, RS 485 cables
Label Printers
THBR 2.0 System - Ambient Conditions Monitoring
RS 232, RS 485 cables

Protective cover for balances
Additional modules
Anti-Draft Chamber for Microbalances
Professional Weighing Tables
Protective cover for balances
Barcode scanners

Anti-Draft Chamber for XA 4Y and XA 5Y Balances
Antistatic ionizer
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter
Under-pan weighing

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]