



More information on the website
radwag.com/us/info,w1,TPE

MYA 0,8/3.5Y Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Moveable range
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Maximum capacity [Max]	0,8/3 g
Minimum load	0,1 mg
Readability [d]	1/10 µg

Verification unit [e]	1 mg
Tare range	-3 g
Standard repeatability [5% Max]	0,6 µg
Standard repeatability [Max]	4,1 µg
Standard minimum weight (USP)	1,2 mg
Standard minimum weight (U=1%, k=2)	0,12 mg
Permissible repeatability [5% Max]	1,2 µg
Permissible repeatability [Max]	6 µg
Linearity	±3/10 µg
Eccentric load deviation	3/10 µg
Sensitivity time drift	1×10 ⁻⁶ /Year×Rt
Stabilization time	3,5 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatyczny - Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, terminal, weighing pan, weighing pan shield, glass lid, power supply, pincette, brush, fabric dust cover.
Weighing chamber dimensions	ø90×90 mm
Weighing pan dimensions	ø16 + ø60 mm
Packaging dimensions	750×492×595 mm
Net weight	9,1 kg
Gross weight	16,6 kg
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max*
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3°C/1h (±1°C/8h)
Relative humidity	40% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
RFID Tags
Antivibration tables

RS 232, RS 485 cables
THBR 2.0 System - Ambient Conditions Monitoring
RS 232, RS 485 cables

Power Adapters
Additional modules
Anti-Draft Chamber for Microbalances
Professional Weighing Tables
Antistatic ionizer
Protective cover for balances
Barcode scanners

Chamber for filter weighing
Weighing dishes
Receipt Printer
Fingerprint Reader
Protective cover for balances
RS 232 – USB Converter

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions

