



More information on the website
radwag.com/br/info,w1,U4E

Bomba de sucção de líquidos

WX-001-0445



The drawings, photos and graphics used are for illustrative purposes only.

Visão geral

Precision suction, error-free measurements The product is supplied with two internal pumps and two built-in buttons used to operate separate pumps. Backlit buttons inform you about operation of a specific pump. The set has two tips for sucking water out of a single beaker (one-channel tip) or four pipettes at a time (four-channel tip). Water is carried from both channels to the beaker through one tube. The power is provided to the pump through a USB A in the weighing terminal. You can supply power from the phone charger, for instance.

Compatível com (Additional Fee)

Balanças automáticas para calibração de micropipetas
Microbalança XA 5Y.M.A
Balança analítica XA 5Y.A

Balança analítica XA 5Y
Microbalança XA 5Y.M
Microbalança MYA 5Y