



More information on the website
radwag.com/tr/info,w1,U4E

Suction pump for liquids



The drawings, photos and graphics used are for illustrative purposes only.

Genel Açıklama

The product is supplied with two internal pumps and two built-in buttons used to operate separate pumps. Backlit buttons inform you about operation of a specific pump.

The set has two tips for sucking water out of a single beaker (one-channel tip) or four pipettes at a time (four-channel tip). Water is carried from both channels to the beaker through one tube.

The power is provided to the pump through a USB in the weighing terminal. You can supply power from the phone charger, for instance.

İle uyumlu

Pipet kalibrasyonu için otomatik teraziler
XA 5Y.M.A Mikro Teraziler
XA 5Y.A Analitik Terazi

XA 5Y Analitik Terazi
XA 5Y.M Mikro Teraziler
MYA 5Y Mikro Terazi