



More information on the website
radwag.com/en/info,w1,U5F

WLC 6/F1/K Precision Balance



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit measurement

Datasheet

| Metrological parameters | |
|-------------------------|--------|
| Maximum capacity [Max] | 6 kg |
| Minimum load | 5 g |
| Readability [d] | 0.1 g |
| Verification unit [e] | 1 g |
| Tare range | -6 kg |
| Repeatability | 0.1 g |
| Linearity | ±0.2 g |
| Stabilization time | 3 s |
| Adjustment | - |

| Metrological parameters | |
|-----------------------------|--|
| OIML Class | II |
| Physical parameters | |
| Leveling system | manualny |
| Display | LCD (backlit) |
| Weighing pan dimensions | 300×300 mm |
| Packaging dimensions | 570×390×170 mm |
| Net weight | 5.2 kg |
| Gross weight | 5.5 kg |
| Construction | |
| Protection class | IP 43 |
| Communication interface | |
| Communication interface | RS232 |
| Electrical parameters | |
| Power supply | Adapter: 100 – 240V AC 50/60Hz 0.6A; 12V DC 1.2A Balance: 10 – 15VDC 0.6A max |
| Operation time on batteries | 10 h (average time) |
| Environmental conditions | |
| Operating temperature | +15 ÷ +30 °C |
| Relative humidity | 10% ÷ 85% RH no condensation |

Repeatability is expressed as a standard deviation from 10 weighing cycles.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.



Accessories

Antivibration Tables
Power Adapters
RS 232 cables (scale - printer)
Stands, wall mounting kits and mounting brackets
Cigarette lighter receptacle power supply cables
Displays
RS 232, RS 485 cables

RS 232 – Ethernet Converter
AP2-1 Current Loop Unit
RS 232, RS 485 cables
RS 232 – USB Converter
RS 232 cables (scale - printer)
RS 232 – RS 485 Converter
Receipt Printer

Software

- RAD Key [WX-010-0005]
- R-Lab [WX-010-0080]

- R-Panel [WX-010-0187]
- Scale Editor 2.1 [WX-010-0173]

Device dimensions





WLC A2



WLC F1/K

WLC F1/R



WLC C2/K

WLC C2/R