



More information on the website  
[radwag.com/us/info,w1,U71](http://radwag.com/us/info,w1,U71)

# CY10.60.C2.K.M2 Precision Balance



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

## Datasheet

Maximum capacity [Max]	60 kg
Minimum load	50 g
Readability [d]	1 g

Verification unit [e]	10 g
Tare range	-60 kg
Repeatability	1,5 g
Linearity	±3 g
Stabilization time	3 s
Adjustment	external
OIML Class	II
<b>Physical parameters</b>	
Leveling system	manual
Display	10" graphic colour touchscreen
Weighing pan dimensions	400×500 mm
Packaging dimensions	720×620×210 mm
Net weight	13,5 kg
Gross weight	16 kg
Cable length	2,5 m
<b>Construction</b>	
Protection class	IP 43
Housing	steel + ABS
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	12÷15V DC
Power consumption	1A
Operating temperature	+15 ÷ +30 °C
Storage temperature	-25 ÷ +70 °C
Relative humidity	10% ÷ 80% RH no condensation

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories

### MediaBox

Mild steel powder coated weighing platforms  
 HRP Platforms High Capacity  
 RFID Tags  
 Power Adapters  
 Additional Weighing platforms Module  
 Mild steel powder coated weighing platforms  
 Additional modules  
 Platforms in plastic casing

### Professional Weighing Tables

Protective cover for balances  
 Barcode scanners  
 RS 232, RS 485 cables  
 Label Printers  
 RS 232, RS 485 cables  
 Receipt Printer  
 Fingerprint Reader  
 RS 232 – USB Converter

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

## Device dimensions

