



More information on the website
radwag.com/en/info,w1,UER

CY10.150.C3.K.M3 Multifunctional Scale



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Metrological parameters

| | |
|------------------------|--------|
| Maximum capacity [Max] | 150 kg |
| Minimum load | 1000 g |

| Metrological parameters | |
|--|--|
| Readability [d] | 50 g |
| Verification unit [e] | 50 g |
| Tare range | -150 kg |
| Max readability for non-verified scale | 5 g |
| Stabilization time | 3 s |
| Adjustment | external |
| OIML Class | III |
| Physical parameters | |
| Leveling system | manualny |
| Display | 10" graphic colour touchscreen |
| Weighing pan dimensions | 500×700 mm |
| Packaging dimensions | 850×800×270 mm |
| Net weight | 22.7 kg |
| Gross weight | 26.5 kg |
| Cable length | 2.5 m |
| Multiple range | YES |
| Construction | |
| Protection class | IP 43 |
| Housing | steel + ABS |
| Communication interface | |
| Communication interface | 2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot |
| Electrical parameters | |
| Power supply | 12÷15V DC |
| Power consumption | 1A |
| Environmental conditions | |
| Operating temperature | -10 ÷ +40 °C |
| Storage temperature | -25 ÷ +70 °C |
| Features of use | |
| Max number of platforms | max.2 |

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
Mild steel powder coated weighing platforms
RFID Tags
Power Adapters
Additional Weighing platforms Module

Protective cover for balances
Barcode scanners
Label Printers
RS 232, RS 485 cables
Fingerprint Reader

Mild steel powder coated weighing platforms
Additional modules
Platforms in plastic casing

RS 232 – USB Converter
Receipt Printer

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]

Device dimensions

