



More information on the website
radwag.com/us/info,w1,UTE

MYA 5.5Y.F1 Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Maximum capacity [Max]	5,1 g
Minimum load	0,1 mg
Readability [d]	1 µg

Verification unit [e]	1 mg
Tare range	-5,1 g
Standard repeatability [5% Max]	0,6 µg
Standard repeatability [Max]	1,6 µg
Standard minimum weight (USP)	1,2 mg
Standard minimum weight (U=1%, k=2)	0,12 mg
Permissible repeatability [5% Max]	1,2 µg
Permissible repeatability [Max]	2,4 µg
Linearity	±5 µg
Eccentric load deviation	5 µg
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times R_t$
Stabilization time	max 8 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatic - Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	manual
Delivery components	Microbalance, terminal, weighing pan, weighing pan for filters, centring ring, power supply, pincette, brush, fabric dust cover.
Weighing chamber dimensions	Ø 168×35 mm
Weighing pan dimensions	Ø160 + Ø26 mm
Packaging dimensions	755×655×455 mm
Net weight	10,2 kg
Gross weight	14,7 kg
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max*
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3°C/1h (±1°C/8h)
Relative humidity	40% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
RFID Tags
Antivibration tables

Barcode scanners
RS 232, RS 485 cables
THBR 2.0 System - Ambient Conditions Monitoring

Power Adapters
Additional modules
Anti-Draft Chamber for Microbalances
Professional Weighing Tables
Antistatic ionizer
Protective cover for balances

RS 232, RS 485 cables
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter
Protective cover for balances

Software

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]