



More information on the website  
radwag.com/us/info,w1,UTE

# MYA 5.5Y.F1 Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

## Datasheet

Maximum capacity [Max]	5,1 g
Minimum load	0,1 mg
Readability [d]	1 µg

Verification unit [e]	1 mg
Tare range	-5,1 g
Standard repeatability [5% Max]	0,6 µg
Standard repeatability [Max]	1,6 µg
Standard minimum weight (USP)	1,2 mg
Standard minimum weight (U=1%, k=2)	0,12 mg
Permissible repeatability [5% Max]	1,2 µg
Permissible repeatability [Max]	2,4 µg
Linearity	±5 µg
Eccentric load deviation	5 µg
Sensitivity time drift	1×10 <sup>-6</sup> /Year×Rt
Stabilization time	max 8 s
Adjustment	internal (automatic)
OIML Class	I
<b>Physical parameters</b>	
Leveling system	automatyczny - Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	manual
Delivery components	Microbalance, terminal, weighing pan, weighing pan for filters, centring ring, power supply, pincette, brush, fabric dust cover.
Weighing chamber dimensions	Ø 168×35 mm
Weighing pan dimensions	Ø160 + Ø26 mm
Packaging dimensions	755×655×455 mm
Net weight	10,2 kg
Gross weight	14,7 kg
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max*
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3°C/1h (±1°C/8h)
Relative humidity	40% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



## Accessories

MediaBox  
RFID Tags  
Antivibration tables

Barcode scanners  
RS 232, RS 485 cables  
THBR 2.0 System - Ambient Conditions Monitoring

Power Adapters  
Additional modules  
Anti-Draft Chamber for Microbalances  
Professional Weighing Tables  
Antistatic ionizer  
Protective cover for balances

RS 232, RS 485 cables  
Receipt Printer  
Fingerprint Reader  
RS 232 – USB Converter  
Protective cover for balances

## Software

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]