



More information on the website  
[radwag.com/en/info,w1,VGR](http://radwag.com/en/info,w1,VGR)

# XA 21.5Y.M Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

- Autotest
- Dosing
- Percent Weighing
- Parts counting
- Peak hold
- Formulation
- Newton unit measurement
- Statistics
- Checkweighing
- IR sensors
- GLP Procedures
- Animal weighing
- Pipettes Calibration
- Air density correction
- Density determination
- Differential weighing
- Ambient conditions monitoring
- Statistical Quality Control
- Packaged Goods Control
- ALIBI Memory
- Wi-Fi

## Datasheet

### Metrological parameters

Maximum capacity [Max]	21 g
Minimum load	0.1 mg

<b>Metrological parameters</b>	
Readability [d]	1 µg
Verification unit [e]	1 mg
Tare range	-21 g
Standard repeatability [5% Max]	1.3 µg
Standard repeatability [Max]	3.5 µg
Standard minimum weight (USP)	2.6 mg
Standard minimum weight (U=1%, k=2)	0.26 mg
Permissible repeatability [5% Max]	2 µg
Permissible repeatability [Max]	5 µg
Linearity	±9 µg
Eccentric load deviation	15 µg
Sensitivity time drift	1×10 <sup>-6</sup> /Year×Rt
Stabilization time	~ 3.5 s
Adjustment	internal (automatic)
OIML Class	I
<b>Physical parameters</b>	
Leveling system	semi-automatic – LevelSENSING
Display	10" graphic colour touchscreen
Weighing chamber doors	manual
Delivery components	Microbalance, weighing pan, weighing pan shield, bottom cover, power supply, brush, fabric dust cover.
Weighing chamber dimensions	168×160×228 mm
Weighing pan dimensions	ø30 mm
Packaging dimensions	750×492×595 mm
Net weight	9.8 kg
Gross weight	16 kg
<b>Construction</b>	
Protection class	IP 43
<b>Communication interface</b>	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
<b>Electrical parameters</b>	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.4A max*
<b>Environmental conditions</b>	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0.3 °C / 1 h (±1 °C / 8 h)
Relative humidity	40% – 80%
Relative humidity change rate	±1% / h (±4% / 8 h)

**Repeatability** is expressed as a standard deviation from 10 cycles of mass standard weighing.

**Stabilization time** depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

\* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

## Accessories

MediaBox  
RFID Tags  
Antivibration Tables  
Power Adapters  
RS 232, RS 485 cables  
Additional modules  
Anti-Draft Chamber for Microbalances  
Professional Weighing Tables  
Protective cover for balances  
Barcode scanners  
Automatic feeders  
MICRO-KIT - Set of Holders for Microscale Glassware

Label Printers  
THBR 2.0 System - Ambient Conditions Monitoring  
RS 232, RS 485 cables  
Protective cover for balances  
Adapters for Pipettes Calibration  
Anti-Draft Chamber for XA 4Y and XA 5Y Balances  
Weighing dishes  
Antistatic ionizer  
Receipt Printer  
Fingerprint Reader  
RS 232 – USB Converter  
Under-pan weighing

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

## Device dimensions

