



More information on the website
radwag.com/ja/info,w1,VGR

XA 21.5Y.M

WL-109-0020



The drawings, photos and graphics used are for illustrative purposes only.



Autotest



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



Newton unit measurement



Statistics



Checkweighing



IR sensors



GLP Procedures



Animal weighing



Pipettes Calibration



Air density correction



Density determination



Differential weighing



Ambient conditions monitoring



Statistical Quality Control



Packaged Goods Control



ALIBI Memory



Wi-Fi



[Max]

21 g

0,1 mg

Wzrost	
Wzrost [d]	1 µg
Wzrost [e]	1 mg
Wzrost	-21 g
Wzrost [5% Max]	1,3 µg
Wzrost [Max]	3,5 µg
Wzrost (USP)	2,6 mg
Wzrost (U=1%, k=2)	0,26 mg
Wzrost [5% Max]	2 µg
Wzrost [Max]	5 µg
Wzrost	±9 µg
Wzrost	15 µg
Wzrost	$1 \times 10^{-6} 700 \text{ mA} - 1 \text{ A} \times R_t$
Wzrost	~ 3,5 s
Wzrost	Wzrost (Wzrost)
OIML	I
Wzrost	
Wzrost	- LevelSENSING
Wzrost	10" Wzrost + Wzrost Wzrost
Wzrost	7Wzrost
Wzrost	, , , , , ,
Wzrost	168×160×228 mm
Wzrost	ø30 mm
Wzrost	750×492×595 mm
Wzrost	9,8 kg
Wzrost	16 kg
Wzrost	
Wzrost	IP 43
Wzrost	
Wzrost	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Wzrost	
Wzrost	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A : 12 – 15V DC 1,4A max*
Wzrost	
Wzrost	+10 – +40 °C
Wzrost	±0,3 °C / 1 h (±1 °C / 8 h)
Wzrost	40% – 80%
Wzrost	±1% / h (±4% / 8 h)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

□□□□□ (Additional Fee)

□□□□□□□□

RFID□□

□□□

□□□□□□

RS 232□RS 485 □□□□

□□□□□□□□

□□□□□□□□□□□□□□

□□□□□□□□□□□□

□□□□□□□□

□□□□□□□□□□

□□□□□□□□

MICRO-KIT - □□□□□□□□□□□□□□□□□□□□

□□□□□□□□

THBR 2.0 □□□□ - □□□□ - □□□□□□□□□□

RS 232□RS 485 □□□□

□□□□□□□□

□□□□□□□□□□□□

XA 4Y□XA 5Y□□□□□□□□□□□□

□□□□

□□□□□□□□□□□□□□

□□□□□□□□

□□□□□□□□

RS 232 – USB □□□□□□

□□□□□□□□

□□□□□ (Additional Fee)

• [WX-010-0099]

• [WX-010-0005]

• [WX-010-0107]

• [WX-010-0173]

• [WX-010-0038]

• [WX-010-0094]

• [WX-010-0080]

• [WX-010-0104]

□□□□□□□□

