



More information on the website  
[radwag.com/us/info,w1,VR9](http://radwag.com/us/info,w1,VR9)

# H315.15.H3.K Waterproof Scale



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

 Plus/Minus Control

 Percent Weighing

 Totalizing

 Parts counting

 Internal battery

 Peak hold

 Newton unit measurement

 Animal weighing

## Datasheet

|  |               |
|--|---------------|
| Maximum capacity [Max]                 | 15 kg         |
| Minimum load                           | 100 g         |
| Readability [d]                        | 5 g           |
| Verification unit [e]                  | 5 g           |
| Tare range                             | -15 kg        |
| Max readability for non-verified scale | 1 g           |
| OIML Class                             | III           |
| <b>Physical parameters</b>             |               |
| Display                                | LCD (backlit) |

| Physical parameters         |   |
|-----------------------------|---|
| Cable length                | 2,5 m   |
| Weighing pan dimensions     | 410×410 mm  |
| Packaging dimensions        | 510×510×270 mm  |
| Net weight                  | 15,5 kg   |
| Gross weight                | 17,3 kg   |
| Construction                |   |
| Protection class            | IP 67 construction, IP 68 (1h max)/69 terminal                  |
| Communication interface     | RS232, USB  |
| Optional interfaces         | RS232 or RS485 or 4IN/4OUT or Ethernet or analog output 4-20 mA |
| Power supply                | 100 – 240 V AC 50/60 Hz   |
| Optional power supply       | internal rechargeable battery                                   |
| Operation time on batteries | max 7h  |
| Operating temperature       | -10 – +40 °C  |
| Relative humidity           | 10% – 85% RH no condensation                                    |



Extra payment for verification



## Accessories

RS 232 cables (scale - printer)  
 Antivibration tables  
 Displays  
 RS 232 cables (scale - Ethernet)  
 RS 232, RS 485 cables  
 RS 232 – Ethernet Converter  
 USB adatper

Receipt Printer  
 USB cable (scale - printer)  
 Stands, wall mounting kits and mounting brackets  
 RS 232 – USB Converter  
 Roller table  
 RS 232, RS 485 cables

## Software

- RAD Key [WX-010-0005]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- R Panel [WX-010-0187]

## Device dimensions



|               |           | A1  | A2  | B       | C1  | C2  | D    | E    | L    |
|---------------|-----------|-----|-----|---------|-----|-----|------|------|------|
| H135...H1.M   | 150 x 200 | 152 | 202 | 87 ± 3  | 110 | 190 | ~443 | ~361 |      |
| H135...H1.K   | 150 x 200 | 152 | 202 | 87 ± 3  | 110 | 146 | -    | -    | 1,5m |
| H315...H2.M   | 250 x 300 | 246 | 306 | 104 ± 3 | 208 | 268 | ~525 | ~483 |      |
| H315...H2.K   | 250 x 300 | 246 | 306 | 104 ± 3 | 208 | 268 | -    | -    | 1,5m |
| H315...H3.M   | 410 x 410 | 410 | 410 | 98 ± 2  | 370 | 370 | ~525 | ~587 |      |
| H315...H3.K   | 410 x 410 | 410 | 410 | 98 ± 2  | 370 | 370 | -    | -    | 2,5m |
| H315...H4.M   | 500 x 500 | 497 | 497 | 155 ± 5 | 400 | 400 | ~767 | ~650 |      |
| H315...H4.K   | 500 x 500 | 497 | 497 | 155 ± 5 | 400 | 400 | -    | -    | 2,5m |
| H315...H3/5.M | 400 x 600 | 597 | 397 | 155 ± 5 | 500 | 300 | ~767 | ~550 |      |
| H315...H3/5.K | 400 x 600 | 597 | 397 | 155 ± 5 | 500 | 300 | -    | -    | 2,5m |
| H315...H5.M   | 600 x 600 | 597 | 597 | 155 ± 5 | 500 | 500 | ~767 | ~750 |      |
| H315...H5.K   | 600 x 600 | 597 | 597 | 155 ± 5 | 500 | 500 | -    | -    | 2,5m |
| H315...H6.M   | 800 x 800 | 799 | 799 | 135 ± 5 | 720 | 740 | ~773 | ~976 |      |
| H315...H6.K   | 800 x 800 | 799 | 799 | 135 ± 5 | 720 | 740 | -    | -    | 2,5m |