



More information on the website
radwag.com/en/info,w1,VUW

DWT/RC HY Checkweigher

WK-106-0___



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| | |
|---------------------------------|-----------------------------------|
| Metrological parameters | |
| Maximum capacity [Max] | 10 – 600 kg |
| Minimum load | 0.1 – 4 kg |
| Readability [d] | 5 – 200 g |
| Tare range | -10 – -600 kg |
| Physical parameters | |
| Display | 5.7" resistive colour touchscreen |
| Construction | |
| Protection class | IP 66 / 67 |
| Communication interface | |
| Communication interface | RS232, RS485 |
| Environmental conditions | |
| Operating temperature | -10 – +40 °C |

Features of use

| | |
|-------------------|----------------|
| Capacity | max 50 pcs/min |
| Conveyor velocity | 0.1 – 0.5 m/s |
| Speed | 0.1 – 0.5 m/s |



Accessories (Additional Fee)

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Keypad, external switches

Receipt Printer

USB cable (scale - printer)

Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]