



More information on the website
radwag.com/en/info,w1,VUW

DWT/RC HY Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	10 - 600 kg
Minimum load	0.1 - 4 kg
Readability [d]	5 - 200 g
Tare range	-10 - -600 kg
Physical parameters	
Display	5.7" resistive colour touchscreen
Construction	
Protection class	IP 66/67
Communication interface	
Communication interface	RS232, RS485
Environmental conditions	
Operating temperature	-10 ÷ +40 °C

Features of use

Capacity	max 50 pcs/min
Conveyor velocity	0.1 ÷ 0.5 m/s
Speed	0.1-0.5 m/s



Accessories

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Keypad, external switches

Receipt Printer

USB cable (scale - printer)

Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]